

1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Product ID: VGABNCMF1



The VGABNCMF1 1-foot Coax HD15 VGA to 5 BNC RGBHV Adapter Cable features an HD15 VGA (male) connector and 5 BNC (RGBHV) (female) connectors, allowing you to connect your existing BNC video source to a VGA distribution amplifier or PC.

The cable can also be used with a VGA out signal, breaking out to 5 BNC female connectors that can be used with a 5 BNC (M-M) cable for use with a BNC monitor/display.

Certifications, Reports and Compatibility



Applications

- Connect your BNC connected cabled panels and projectors to a VGA distribution amplifier or PC

Features

- Short flexible cable design
- HD15 VGA Male to 5 BNC Female Connectors

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
Connector(s)	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	5 - BNC (RF Coax) Female
Special Notes / Requirements	Note	RGB signal: Red, Green, Blue wires, Vertical Sync: Black wire, Horizontal Sync: White wire
Physical Characteristics	Cable Length	1 ft [0.3 m]
	Cable OD	0.3 in [8.5 mm]
	Color	Black
	Product Length	1 ft [0.3 m]
	Weight of Product	3.6 oz [103 g]
	Wire Gauge	28 AWG
Packaging Information	Package Height	0.7 in [17 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	3.8 oz [108 g]
What's in the Box	Included in Package	1 - 1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Product appearance and specifications are subject to change without notice.