

Date of Declaration: September 16, 2019

Declaration of Conformity

Product Number	Description
PXT100	6 ft Standard Computer Power Cord Extension - C14 to C13

To whom it may concern,

I declare that this declaration is issued under the sole responsibility of StarTech.com and that the above product conforms to all the applicable requirements of Directives and Regulations as indicated in this document.



Nirav Gandhi
Vice President, Product Development

StarTech.com Ltd.

e. prodcompliance@startech.com

t. (800) 265-1844

f. (519) 455-9425

Regulations**Test Standards****RoHS Directive**

2011/65/EU & 2015/863

REACH Regulation

EC 1907/2016

This StarTech.com part number is in compliance with the European Directive 2011/65/EU on the Restriction of Hazardous Substances (RoHS) that include Pb, Hg, Cd, Cr6+, PBB, and PBDE. The product is also compliant to the amendment Directive (EU) 2015/863, which added four more substances that include DEHP, BBP, DBP, and DIBP. The RoHS exemptions that apply to this product are: 6(c).

This product is also compliant with the REACH Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18 December 2006, concerning the Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH). The product and its components do not contain any of the Candidate listed 197 Substances of Very High Concern (SVHC) above the threshold of 0.1% by weight. None of the 68 Restricted Substances listed in Annex XVII are present in excess of thresholds set by the regulation.

Persistent Organic Pollutants (POPs)

EC No 850/2004

As per the EU Persistent Organic Pollutants Regulation (EC) No 850/2004 and Stockholm Convention, this StarTech.com product is free of the listed substance or falls under an exemption.

WEEE Directive

2003/108/EC

The European Directive 2012/19/EU on Waste Electrical and Electronic Equipment (WEEE)

Packaging Directive

94/62/EC

The European Packaging and Packaging Waste Directive 94/62/EC

North American Safety**UL Listing ID**

E94923, E135710

UL Standard

ANSI/UL 817, CSA-C22.2 No. 21, ANSI/UL 62, CSA-C22.2 No. 49